

CAUTION - CORROSIVE

KEEP OUT OF REACH OF CHILDREN

READ SAFETY DIRECTIONS BEFORE OPENING OR USING

STAINEX⁺ CLEANER LIGHT

Highly concentrated cleaner for stainless steel, non-ferrous metals and aluminium.

- ◆ Removes teastains, rust, lime veil as well as oil and grease
- ◆ Will not damage or discolour the base metal
- ◆ Highly viscous - optimal adhesion to vertical surfaces
- ◆ Does not contain hydrofluoric, nitric or hydrochloric acids

APPLICATION: Apply STAINEX-CLEANER with a brush, allow time to react. Rinse off with water. If necessary, use non-abrasive brush or sponge. Can be diluted with water up to 1:40 (viscosity decreases). Food contact surfaces must be rinsed with water after cleaning (leaves no residue). To maintain cleaned surface, use **STAINEX-CARE**. Note: intended for use on described materials only, test on other materials before use.

SAFETY DIRECTIONS DO NOT SWALLOW. Irritating to eyes and skin. Wear protective gloves. In case of contact with eyes rinse immediately with plenty of water and seek medical advice. In case of accident or if you feel unwell, seek medical advice immediately.

CONTAINS PHOSPHORIC ACID
less than 200g/kg

STAINEX⁺

by DRIZIGN PTY LTD
abn 66 085 088 580

43 Henderson Rd Clayton North 3168
po box 295 Oakleigh 3166, Victoria, Aus
p: 613 9562 5244 f: 613 9562 5277

e: contactus@stainex.com.au w: stainex.com.au

STAINEX⁺ CLEANER LIGHT

1L



Highly concentrated cleaner for stainless steel.

by drizign